

ø52mm Planetary Gear Motor Carbon - Brushed

MOT-I-81636-52-12

Online ID:

PGM-52-24-12-500-02

Our Planetary Gear Motors are an inline solution providing excellent torque output at various speeds. They are equiped to handle varying loads and are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.



Contact Us for alternative solutions!

Specifications	
Gearhead Type:	Planetary
Motor Type:	Carbon - Brushed
Rated Voltage:	24V DC
Rated Speed:	395 rpm
Rated Torque:	10 kg.cm
Rated Current:	4 A

No-Load Speed:	500 rpm (+/- 10%)
No-Load Current:	< 1.7 A
Max. Power:	63 W
Reduction Ratio:	12:1
Bearing Type:	Ball Bearing
Termination Style:	Terminals





