







ISS.	AMEND	DATE
1	ISSUED	05/07/21
2	ADD 22AWG-26AWG	14/10/21

DUAL MOUNT
CAN BE FRONT OR REAR MOUNTED



SUPPLIED WITH COVER



Ø3.20 PLAIN HOLE
CP30727MBX1

VARIANTS	
PART NO.	HOLE DETAILS
CP30727MB	HOLE Ø3.2 x CSK 90° x Ø5.85
CP30727MB3	M3 HOLES
CP30727MB440	#4-40 HOLES
CP30727MBX1	PLAIN HOLE Ø3.2

4x HOLE VARIANTS
Ø3.2mm CSK 90° x Ø5.85
M3 x 0.5 THREAD
#4-40 UNC THREAD
PLAIN Ø3.2 HOLES

Material:

1. RJ45 / IDC / Cover : PC
2. RJ45: Phosphor Bronze, gold plated
3. IDC: Phosphor Bronze, nickel plated
4. PCB: FR4
5. Frame: Diecast, Black


Performance:

1. T568A + T568B wiring.

RoHS
COMPLIANT

TOLERANCE
NO DEC. PLACE ±
1 DEC. PLACE ±
2 DEC. PLACE ±
HOLE Ø ±
ANGLES ±
UNLESS
OTHERWISE STATED

NOTE COVER
NOT SHOWN



Cliff Electronic Components Ltd.

76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

3rd ANGLE PROJECTION:

DO NOT SCALE

MATERIAL: SEE NOTES

FINISH: SEE NOTES

DRAWN: T.J.O.

APPROVED: D.P.J.

TITLE: DUAL MOUNT SLIM BLACK METAL CAT6 IDC

DRWG. No. CP30727MB

FORM: A4DRWGH