

Part Number: RBC18-PWH

Compatibility

Guaranteed UPS compatibility, meets or exceeds UPS manufacturer specifications

All new components (batteries, connectors, metal tray, cables) - No Refurbished Parts

Includes: All required connectors, Battery recycling guide, Installation guide, Metallic battery tray or enclosure, Reusable packaging

Ease of Use

Fully assembled for easy (hot swappable) installation - No Assembly Required

Tested, charged and ready for installation out of the box

Assembled in USA

Installation and Recycling guide included with product

Re-usable packaging with clear instructions on how to properly dispose of spent batteries

Technical Specifications

Battery

Battery Type	Maintenance Free Sealed Lead-Acid Battery (leak proof)
Battery Mounting	Enclosed cartridge
RBC Quantity	1
Voltage	24V

Environmental

Operating Temperature	32° to 104° F (0° to 40° C)
Storage Temperature	5° to 113° F (-15° to 45° C)

Physical

Product Dimensions	4.0" L x 11.90" W x 1.40" H
Product Weight	5.70 lbs
Shipping Dimensions	4.68" L x 12.25" W x 2.50" H
Shipping Weight	7.0 lbs