## Part Number: RBC6-PWH

## Compatibility

Guaranteed UPS compatibility, meets or exceeds UPS manufacturer specifications

All new components (batteries, connectors, metal tray, cables) - No Refurbished Parts

Includes: All required connectors, Battery recycling guide, Installation guide, Metallic battery tray or enclosure, Reusable packaging

## Ease of Use

Fully assembled for easy (hot swappable) installation - No Assembly Required

Tested, charged and ready for installation out of the box

Assembled in USA

Installation and Recycling guide included with product

Re-usable packaging with clear instructions on how to properly dispose of spent batteries

## **Technical Specifications**

Battery	
Battery Type	Maintenance Free Sealed Lead-Acid Battery (leak proof)
Battery Mounting	Enclosed cartridge
RBC Quantity	1
Voltage	24V
Environmental	
Operating Temperature	32° to 104° F (0° to 40° C)
Storage Temperature	-15° to 45° C
Physical	
Product Dimensions	7.70" L x 6.00" W x 3.70" H
Product Weight	16.90 lbs
Shipping Dimensions	11.25" L x 9.25" W x 8.00" H
Shipping Weight	18 lbs