

TKG-105-IP68-GREY

InduProof 2



TKG-105-IP68-BLACK

InduProof 2



PRODUCT FEATURES

- Silicone keyboard with 105 keys
- Long lasting mechanical short stroke switches
- IP68 protection, can be submerged into liquids
- Can be cleaned with soapy water, disinfectants or other cleaning agents
- Special coating for excellent mechanical and chemical

SPECIFICATION

Number of keys:	105	USB compatibility:	complies with USB 2.0
Housing type:	desktop housing	Operating temperature:	-20 °C to +70 °C
Housing / bottom material:	silicone / aluminium	Storage temperature:	-25 °C to +80 °C
Colour:	grey, black	Dimensions:	387 x 150 x 22 mm
Keyswitch technology:	short travel keys	Weight:	approx. 1200 g
Switching cycles:	approx. 3 mill. (per key)	Compliance:	
Operating force:	2.6 N	-- Europe:	CE
Switch travel:	0.3 mm	-- USA/Canada:	FCC Part 15 Class B
Protection level:	IP68	-- Global:	REACH, RohS self-declaration
Interface:	USB		

Cat.No.	Product description	Housing colour	Layout
KG02004	TKG-105-IP68-GREY-USB-DE	Grey	German
KG02005	TKG-105-IP68-GREY-USB-US	Grey	US
KG02440	TKG-105-IP68-BLACK-USB-DE	Black	German
KG02435	TKG-105-IP68-BLACK-USB-US	Black	US

Other language versions / interfaces / configurations available on request.

Subject to modifications and errors