

VFA 1-230-5M35

35mm Focal Length

2/3" F1.4/35 C-Mount			
Focal Length		f=35mm	
Max Diameter(RATIO)		F=1:1.4~16	
Picture Size		2/3"	1/2"
Angle	H	30.3°	22.3°
	V	23°	16.8°
	D	37.3°	27.8°
Object Dimension at M.O.D	H	170.4mm	123.7mm
	V	127.6mm	92.7mm
	D	212.8mm	154.9mm
Distortion(TV)		<0.1%	<0.3%
Focus distance(min)		0.2m	
Flange back		17.526mm in air	
Back focus		9.2mm in air	
Filter screw size		M30.5x0.5	
Front/Rear Effective Dia		Front Φ 22.7mm Rear Φ 12.6mm	
Mount		C-Mount	
Temperature Range		-10~+50°C	
Storage Temperature Range		-20~+60°C	

