

VFA4-111-20M12

12mm focal length

Model	VFA4-111-20M12		
Resolution ratio	20M Pixels		
Mount	C		
Sensor	1.1"		
Focal Length	12mm		
F.NO	F=1:2.8-16		
Focus Distance	0.1M—∞		
Flange back	17.526mm		
Back focus	10.31mm		
Rel.illumination	≥65%		
Front/Rear Effective Dia	Φ25.8/Φ13.5		
Sensor		1.1"	1 "
Field of View	D	72.7°	67.9°
	H	61.9°	56.9°
	V	47.5°	44.1°
TV DISTORTION	<0.1%		
Working temperature	-40°C~80°C		
Storage temperature	-40°C~85°C		

