

VFA4-230-5M12

12mm Focal Length

2/3" Full C-Mount		
Focal Length	f=12mm	
Resolution	5 Megapixel	
Aperture (Close)	F=1:1.6~16	
Angle of view	1"	/
	1/2"	36°x29.2°x22.1°
	2/3"	48.1°x39.4°x30.1°
Distortion(TV)	<0.15%	
Focus distance(min)	0.1m~1.5m	
Flange back	17.526mm in air	
Back focus	14.04mm in air	
Mount	C-Mount	
Weight		

