

VFA4-230-5M16

16mm Focal Length

		2/3" Full C-Mount
Focal Length		f=16mm
Resolution		5 Megapixel
Aperture (Close)		F=1:1.6~16
Angle of view	1"	/
	1/2"	28°x22.5°x17°
	2/3"	37.8°x30.7°x23.2°
Distortion(TV)		<0.1%
Focus distance(min)		0.1m~1.5m
Flange back		17.526mm in air
Back focus		14.9mm in air
Mount		C-Mount
Weight		

