

## CLEANTYPE® EASY PROTECT COMPACT

KSI-U10300 (WHITE)

KSI-U20300 (BLACK)



## SPECIAL FEATURES

- IP68 rated medical and industrial keyboard with silicone cover
- Washable rated medical and industry keyboard
- Waterproof silicone cover
- Integrated Clean Mode for cleaning
- EN60601-1-2 Ed 4, EN61000-6-2 certified

## SPECIFICATION

Number of keys:	88 (US-layout)	Cable length:	15cm
Keyswitch technology:	Membrane switch	Operating temperature:	0°C ~ +55°C
Switching cycles:	Approx.2mill. (per key)	Storage temperature:	-10°C ~ +60°C
Housing material:	Plastic	Dimensions:	302 (L) x 151.5 (W) x 21 (H) mm
Cover material:	Silicone	Weight:	485+/-10 g
Housing colour:	White & black	Warranty:	2 years
Protection level:	IP68 (acc.to IEC 60529-2013)	Certification:	EN60601-1-2 Ed 4, CE, FCC, EN61000-6-2
Interfaces:	USB		

## SUPPLEMENT PRODUCTS

Cat. No.	Product Description	Color	Layout
KSI-U10300-US	EASY PROTECT COMPACT, IP68, USB 15cm with waterproof cap	White	US
KSI-U20300-US	EASY PROTECT COMPACT, IP68, USB 15cm with waterproof cap	Black	US

Other layouts, configurations and interfaces on request.

## EN60601-1-2 ED 4 AND EN61000-6-2 CERTIFIED

EN60601-1-2 Ed 4 applies to the basic safety and essential performance of Medical Equipment (ME) equipment and ME systems in the presence of electromagnetic disturbances and to electromagnetic disturbances emitted by ME equipment and Me systems. EN61000-6-2 applies to the industrial equipment.

## SHORT OPERATING INSTRUCTIONS



Press and hold Clean on/off key for 5s to enable Clean Mode. Clean Mode is indicated by the lock icon indicator light.

## CLEANING INSTRUCTION

For further details please refer to below link:

<https://gett-group.com/en/gett-service/cleaning-and-material-resistances>