

**CLEANTYPE®**

**WATERPROOF  
MEDICAL MOUSE**

MPL-U10010 (WHITE)

MPL-U20010 (BLACK)



**SPECIAL FEATURES**

- IP68 rated medical mouse
- 1.4M cable length
- Easy to clean and disinfect
- Comfortable use
- Use special designed plastic scroll

**SPECIFICATION**

Number of keys:	3	Interfaces:	USB
Scanning:	Optical detection + 800DPI resolution	Operating temperature:	0°C ~ +55°C
Switching cycles:	Approx. 3 mill. (per key)	Storage temperature:	-10°C ~ +60°C
Protection level:	IP68	Dimensions:	115(L) x 61.6(W) x 36(T)mm
Housing material:	Plastic	Weight:	Approx.115g
Housing color:	White & black	Certification:	CE, RoHS, REACH
		Warranty:	2 years

**ORDER INFORMATION**

Cat. No.	Product Description	Color
MPL-U10010	Waterproof medical wheel scroll optical plastic mouse	White
MPL-U20010	Waterproof medical wheel scroll optical plastic mouse	Black

Other detections, configurations and interfaces on request.

**CLEANING INSTRUCTION**

For further details please refer to below link:

<https://gett-group.com/en/gett-service/cleaning-and-material-resistances>