

CLEANTYPE[®] 2.4G WIRELESS MEDICAL MOUSE

MSI-G10010 (WHITE)
MSI-G20010 (BLACK)



SPECIAL FEATURES

- IP65 rated medical mouse
- 2.4G wireless connection
- Fully washable and disinfect able
- Excellent tactile feeling

SPECIFICATION

Number of keys:	5	Operating temperature:	0°C ~ +55°C
Scanning:	optical detection +800DPI resolution	Storage temperature:	-40°C ~ +70°C
Switching cycles:	approx. 2 mill. (per key)	Dimensions:	115(L) x 61.5(W) x 42(T) mm
Protection level:	IP65	Weight:	approx. 106g
Housing material:	silicone	Certification:	CE, RoHS
Housing colour:	white & black	Warranty:	2 years
Interfaces:	2.4G wireless connection		

ORDER INFORMATION

Cat. No.	Product description	Colour
MSI-G10010	2.4G Wireless Medical Mouse	White
MSI-G20010	2.4G Wireless Medical Mouse	Black

Other detections, configurations and interfaces on request.

CLEANING INSTRUCTION

For further details please refer to below link:
<http://www.gett-group.com/content/service-cleaning-instructions>