

TKG-086-IP68-WHITE
InduProof® Smart Compact



SPECIAL FEATURES

- Compact silicone keyboard with 86 keys incl. num pad
- IP68 protection, can be submerged into liquids
- Can be cleaned with soapy water, disinfectants or other cleaning agents
- KeyLock function to disable the keys while cleaning the keyboard
- Ergonomic design
- Flat key profile for easy cleaning
- Comfortable typing
- Compact dimensions

SPECIFICATION

Number of keys:	86	Interfaces:	USB
Keyswitch technology:	carbon contacts	Cable length:	2 m
Operating force:	1.5 N	Operating temperature:	-25 °C to +75 °C
Switch travel:	1.0 mm	Storage temperature:	-30 °C to +75 °C
Switching cycles:	approx. 2 mill. (per key)	Dimensions:	305 x 150 x 11 mm
Protection level (max):	IP68	Weight:	approx. 685 g
Housing material:	silicone	Certifications:	CE, FCC
Housing colour:	white	Guarantee:	3 years *

ORDER INFORMATION

Cat.No.	Product description	Colour	Layout
KG20230	TKG-086-IP68-WHITE-USB-DE	white	German
KG20231	TKG-086-IP68-WHITE-USB-US/EU	white	US / EU
KG21247	TKG-086-IP68-WHITE-USB-CH	white	Switzerland
KG21204	TKG-086-IP68-WHITE-USB-FR	white	French
KG23253	TKG-086-IP68-WHITE-USB-IT	white	Italian
KG21226	TKG-086-IP68-WHITE-USB-SKAN	white	Scandinavian
KG21223	TKG-086-IP68-WHITE-USB-UK	white	UK English
KG22304	TKG-086-IP68-WHITE-USB-US/ARAB	white	US Arabic

Other language versions / Interfaces / configurations available on request.

SILICONE PC MICE COMPLEMENTARY TO THE KEYBOARD

Cat.No.	Product description	Colour
KH20225	TKH-MOUSE-SCROLL-IP68-WHITE-LASER-USB	white

* on the electric function

Subject to modifications and errors