



General ordering data

Order No.	1938600000
Part designation	SAI-AU M8 SB 8DI
Version	Sensor-actuator active distributor, Sub-bus, Complete module
EAN	4032248612611
Qty.	1 pc(s).

Technical data of bus system

Baud rate	automatic
Bus user	15
Diagnosis indication	red
Station addresses	automatic

Technical data

Behaviour in fire	5VA
Bus system	Sub-bus
Digital inputs	8
Electrical isolation available	No
Operating temperature, max.	60 °C
Operating temperature, min.	0 °C
Ordering data, title	SAI-AU Digital
Protection class	IP 67
Rated voltage	24 V DC (20.4...28.8 V)
Storage temperature, max.	85 °C
Storage temperature, min.	-25 °C
Total current	4 A 8 A

Technical data, snap-on modules

Digital input type	TYPE 1 to EN 61131-2
E/A function indicator	LED yellow
Insulation material of housing	PBT
Output level	Short-circuit-protected
Sensor voltage indicator	LED green
max. current-carrying capacity per output signal	0.5 A 2 A

Technical data, snap-on modules

Approvals

Approvals institutes



Classifications

ETIM 3.0	EC001597
eClass 5.1	27-25-04-03

Similar products

Order No.	Part designation	Version
1938630000	SAI-AU M8 SB 8DIO	Sensor-actuator active distributor, Sub-bus, Complete module
1938660000	SAI-AU M8 SB 8DO 2A	Sensor-actuator active distributor, Sub-bus, Complete module