## **DK** ELECTRIC DOUBLE LAYER CAPACITORS "DYNACAP"



High Voltage Tolerance Capacitors GREEN CAP

- High voltage tolerant(6.3V guaranteed) and highly reliable.
- Ideal for backing up of Li-battery-backed equipment such
- as cameras, VCR's and telephone sets.



70°C




Marking color : White print on an indigo sleeve

## Specifications

| Item  | Performance   |  |            |      |      |     |  |
|---|---|--|------------|------|------|-----|--|
| Category temperature range (°C)             | -25 to +70  |  |            |      |      |     |  |
| Folerance at rated capacitance (%)          | -20 to +80  |  |            |      |      |     |  |
| Internal resistance                         | Rated Capacitance (F)                                   | 0.047  | 0.1        | 0.47 | 0.68 | 1.0 |  |
| at 1 kHz                                    | Internal resistance (Ω)                                 | 300  | 200        | 50   | 50   | 30  |  |
| Characteristics at high and low temperature | Percentage of capacitance change<br>Internal resistance | Within ±30% of the value at 20°C   less than five times of the value at 20°C |            |      |      |     |  |
|   | Test time   |  | 1000 hours |      |      |     |  |
| Endurance (70°C)                            | Percentage of capacitance change                        | Within ±30% of the initial measured value                                    |            |      |      |     |  |
|   | Internal resistance                                     | Within four times of the initial specified value                             |            |      |      |     |  |
| Shelf life (70°C)                           | Test time :1000 hours ; Same as endurance.              |  |            |      |      |     |  |

## **Outline Drawing**



| Part numbering system (example: 6.3V0.1F) |    |                      |                             |   |     |   |
|---|----|----------------------|-----------------------------|---|-----|---|
|   | DK | _                    | 6R3                         | D | 104 | т |
| Series code                               |    | Rated voltage symbol | Rated capacitance<br>symbol |   |     |   |

Part number is refer to below table.

## Standard Ratings

| Max. operating voltage(V) | Rated capacitance(F) | ELNA Parts No. | ø DxL(mm) |
|---------------------------|----------------------|----------------|-----------|
| 6.3                       | 0.047                | DK-6R3D473T    | 13.5x9.5  |
| 6.3                       | 0.1                  | DK-6R3D104T    | 13.5x9.5  |
| 6.3                       | 0.47                 | DK-6R3D474T    | 21.5x9.5  |
| 6.3                       | 0.68                 | DK-6R3D684T    | 21.5x9.5  |
| 6.3                       | 1.0                  | DK-6R3D105T    | 21.5x9.5  |