This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited. ©2021, PUI Audio Inc.




Data Sheet

AB1541B-6

Specifications

Parameters	Values	Units
Resonant Frequency	4,100 ± 500	Hz
Resonant Impedance (Max)	1000	Ohms
Max Input Voltage	30	Vp-p
Capacitance (@ 1 kHz)	8000 ± 30%	pF
Plate Material	Brass	-
Storage Temperature	-20 ~ +70	°C
Operating Temperature	-20 ~ +60	°C
Environmental Status	ROHS/REACH	Exempt. 7c-1


Dimensions




www.puiaudio.com

This document contains data proprietary to PUI Audio Inc. Any use or reproduction, in any form, without prior written permission of PUI Audio Inc. is prohibited. ©2021, PUI Audio Inc.

Packaging





Тгау	90mm x 100mm	5 x 5 = 25pcs
Bag	120mm x 170mm	25 x 40 = 1,000pcs
Vacuum Seal	280mm x 260mm	25 x 40 x 4 = 4,000pcs
Outer Box	330mm x 245mm x 50mm	25 x 40 x 4 = 4,000pcs
Carton	550mm x 330mm x 290mm	4000 x 10 = 40,000pcs

Specifications Revisions

Revision	Description	Date
А	Released from Engineering	10/1/2021

Note:

- 1. Unless otherwise specified:
 - A. All dimensions are in millimeters.
 - B. Default tolerances are ± 0.5 mm and angles are $\pm 3^{\circ}$.
- 2. Specifications may not change without prior customer approval.