


P1:	M-Y139A M-139B
P2,P3:	M-Y139H M-139H
P4:	M-426E



1E13		
P2	P1	P3
1	1	1 BROWN
2	2	2 RED
3	3	3 ORANGE
4	4	4 YELLOW
5	5	5 GREEN
6	6	6 BLUE
7	7	7 PURPLE
8	8	8 GRAY
9	9	9 BLACK
SHIELD	SHIELD	SHIELD

NOTE: All relevant materials are complied with RoHS directive .

No.	DESCRIPTION	Q'TY	Supplier
5&6	BLACK PVC TUBE $\phi$ 3.0*22mm	3	M304
	ALUMINUM FOIL 33*65mm	3	M309
	MOLDED PE COLOR TRANSPARENT		M280
	MOLDED PVC BEIGE		M304
4	NON-UL 9C 28AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, OD 5.0mm, JACKET BEIGE, DRAWING No. EMAL2809C-051	290mm*2	M304
3	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, BEIGE	6	M95
2	DB9 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	2	M277
1	DB9 MALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	1	M277

APPROVED		<p><b>COMPUCABLEPLUS</b> PROVIDING CONNECTIVITY SOLUTIONS</p>	Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm
CHECKED	HU		
DRAWING	ZHU		
DATE	05/JULY/19	ITEM NO.	DMC-9MF-01B & DMC-9MF-01B-MF
		UNIT:mm	