


P1,P2: M-Y139C  
M-139H  
P3: M-426E

Customer No: \_\_\_\_\_



1003			
P1		P2	
1	—————	1	BROWN
2	—————	2	RED
3	—————	3	ORANGE
4	—————	4	YELLOW
5	—————	5	GREEN
6	—————	6	BLUE
7	—————	7	PURPLE
8	—————	8	GREY
9	—————	9	BLACK
SHIELD	—————	SHIELD	

\* NOTE: All relevant materials are complied with RoHS directive .

No.	DESCRIPTION	Q'TY	Supplier
4	BLACK PVC TUBE $\phi$ 3.0*22mm	2	M304
	ALUMINUM FOIL 33*65mm	2	M309
	MOLDED PE COLOR TRANSPARENT		M280
	MOLDED PVC BEIGE		M304
3	NON-UL 9C 28AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, OD 5.0mm, JACKET BEIGE, DRAWING No. EMAL2809C-051	L-20mm	M304
2	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, BEIGE	4	M95
1	DB9 MALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	2	M277

APPROVED		<p><b>COMPUCABLEPLUS</b>  PROVIDING CONNECTIVITY SOLUTIONS</p>	Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm
CHECKED	HU		
DRAWING	ZHU		
DATE	05/JULY/19	ITEM NO.	DMC-9MM-XXB & DMC-9MM-XXB-MF
		UNIT:mm	