



△*NOTE: ALL relevant materials are complied with ROHS directive

2057	
P1	P2
1	1 BROWN
2	3 RED
3	2 ORANGE
4	5 YELLOW
5	4 GREEN
6	20 BLUE
8	
7	7 PURPLE
20	6 BLACK
	8
SHIELD	SHIELD

6	Jumper Wire UL1061/28#/1C x 28mm ID0.0.9 DRAWING NO.EH002801C-024	H5SE07-0304	1	M304
	BLACK PVC TUBE ϕ 3.0*30mm	H7A001-0304K09	1	M304
	ALUMINUM FOIL 33*110mm	A6MA05-0309	1	M309
	MOLDED PE COLOR TRANSPARENT	A5BA02-0280		M280
	MOLDED PVC BEIGE	H1BF01-0304B01		M304
5	Jumper Wire UL1061/28#/1C x 28mm ID0.0.9 DRAWING NO.EH002801C-024	H5SE07-0304	1	M304
	BLACK PVC TUBE ϕ 3.0*30mm	H7A001-0304K09	1	M304
	ALUMINUM FOIL 33*110mm	A6MA05-0309	1	M309
	MOLDED PE COLOR TRANSPARENT	A5BA02-0280		M280
4	MOLDED PVC BEIGE	H1BF01-0304B01		M304
	NON-UL 8C 28AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, OD 5.0mm, JACKET BEIGE, DRAWING No. EMAL2808C-045	H5BL27-0304B01	Lmm	M304
	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, BEIGE	H1RB01-0304B01 A6AA30-0095	4	M95
	DB25 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	A1AE01-0277U09	1	M277
1	DB25 MALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	A1AE09-0277U09	1	M277
No.	DESCRIPTION		Q'TY	Supplier

APPROVED		<p>COMPUCABLEPLUS PROVIDING CONNECTIVITY SOLUTIONS</p>	Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm		
CHECKED	HU				
DRAWING	ZHU				
DATE	05/JULY/19	ITEM NO.	DNC-25MF-XXB & DNC-25MF-XXB-MF	UNIT:mm	