





| | |
|-----|---------|
| P1: | M-Y139C |
| | M-139H |
| P2: | M-Y222A |
| | M-222A |
| P3: | M-426E |



△*NOTE: ALL relevant materials are complied with ROHS directive
Logo on double sides of overmold.



| | | | | |
|-----|---|-------------------------------|--------|----------|
| 6 | BLACK PVC TUBE ϕ 3.0*30mm | H7A001-0304K09 | 1 | M304 |
| | ALUMINUM FOIL 33*110mm | A6MA05-0309 | 1 | M309 |
| | MOLDED PE COLOR TRANSPARENT | A5BA02-0280 | | M280 |
| | MOLDED PVC BEIGE | H1BF01-0304B01 | | M304 |
| 5 | BLACK PVC TUBE ϕ 3.0*22mm | H7A001-0304K09 | 1 | M304 |
| | ALUMINUM FOIL 33*65mm | A6MA05-0309 | 1 | M309 |
| | MOLDED PE COLOR TRANSPARENT | A5BA02-0280 | | M280 |
| 4 | MOLDED PVC BEIGE | H1BF01-0304B01 | | M304 |
| | NON-UL 8C 28AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, OD 5.0mm, JACKET BEIGE, DRAWING No. EMAL2808C-045 | H5BL27-0304B01 | L-20mm | M304 |
| | MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, BEIGE | H1RB01-0304B01 A6AA30-0095 | 4 | M95 |
| 2 | DB25 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR | A1AE01-0277U09 | 1 | M277 |
| 1 | DB9 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR | A1AA01-0277U09 | 1 | M277 |
| No. | DESCRIPTION | | Q'TY | Supplier |

| | | | |
|----------|------------|--|--|
| APPROVED | |  COMPUCABLEPLUS PROVIDING CONNECTIVITY SOLUTIONS | Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm |
| CHECKED | HU | | |
| DRAWING | ZHU | | |
| DATE | 05/JULY/19 | ITEM NO. | DNC-9F25F-XXB & DNC-9F25F-XXB-MF |
| | | UNIT:mm |  |