


P1:	M-Y139C
	M-139H
P2:	M-Y222E
	M-222D
P3:	M-426E



① \*NOTE: ALL relevant materials are complied with ROHS directive



6	BLACK PVC TUBE $\phi 3.0 \times 30\text{mm}$	H7A001-0304K09	1	M304
	ALUMINUM FOIL 33*110mm	A6MA05-0309	1	M309
	MOLDED PE COLOR TRANSPARENT	A5BA02-0280		M280
	MOLDED PVC BEIGE	H1BF01-0304B01		M304
5	BLACK PVC TUBE $\phi 3.0 \times 22\text{mm}$	H7A001-0304K09	1	M304
	ALUMINUM FOIL 33*65mm	A6MA05-0309	1	M309
	MOLDED PE COLOR TRANSPARENT	A5BA02-0280		M280
	MOLDED PVC BEIGE	H1BF01-0304B01		M304
4	NON-UL 8C 28AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, OD 5.0mm, JACKET BEIGE, DRAWING No. EMAL2808C-045	H5BL27-0304B01	L-20mm	M304
3	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, BEIGE	H1RB01-0304B01 A6AA30-0095	4	M95
2	DB25 MALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	A1AE09-0277U09	1	M277
1	DB9 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	A1AA01-0277U09	1	M277
No.	DESCRIPTION		Q'TY	Supplier

APPROVED		<p><b>COMPUCABLEPLUS</b> PROVIDING CONNECTIVITY SOLUTIONS</p>	Cable Length Unless Other Spec. Tolerances:	
CHECKED	HU		0 ~200mm	±10mm
DRAWING	ZHU		201~1000mm	±20mm
DATE	05/JULY/19	ITEM NO.	DNC-9F25M-XXB & DNC-9F25M-XXB-MF	UNIT:mm
				1001 ~1500mm ±25mm 1501 ~2100mm ±30mm 2100mm↑ ±40mm