


P1,P2: M-Y139C
M-139C
P3: M-426E

Customer No: No:4



* NOTE: All relevant materials are complied with RoHS directive .

5&6	BLACK PVC TUBE $\phi 3.0 \times 22\text{mm}$	A7A001-0304K09	2	M304
	ALUMINUM FOIL 33*65mm	A6MA05-0309	2	M309
	MOLDED PE COLOR TRANSPARENT	A5BA02-0280		M280
	MOLDED PVC BEIGE	H1BF01-0304B01		M304
4	NON-UL 7C 28AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, OD 4.0mm, JACKET BEIGE, DRAWING No. EMAL2807C-040	H5BL23-0304B01	L-20mm	M304
3	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, BEIGE	H1RB01-0304B01 A6AA30-0095	4	M95
2	DB9 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	A1AA01-0277U09	1	M277
1	DB9 MALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	A1AA12-0277U09	1	M277
No.	DESCRIPTION		Q'TY	Supplier

APPROVED		<p style="margin: 0;">COMPUCABLE PLUS PROVIDING CONNECTIVITY SOLUTIONS</p>	Cable Length Unless Other Spec. Tolerances:	
CHECKED	HU		0 ~200mm	±10mm
DRAWING	ZHU		201~1000mm	±20mm
DATE	05/JULY/19		1001 ~1500mm	±25mm
	ITEM NO.	DNC-9MF-XXB & DNC-9MF-06B-MF	1501~2100mm	±30mm
			2100mm↑	±40mm
			UNIT:mm	