

## ø 36mm DC Motor Carbon - Brushed

MOT-HS36-2685

Online ID#: BDC-HS36-50.5-12-3650-S

Our DC Motors are a cost-effictive solution for any application. They offer simple integration and come in a variety of sizes. With endless performance combinations, we have a tailored motor solution for you.





## Contact Us for alternative solutions!

| Specifications |                  |
|----------------|------------------|
| Motor Type:    | Carbon - Brushed |
| Rated Voltage: | 12V DC           |
| Rated Speed:   | 3,025 rpm        |
| Rated Torque:  | 206 g.cm         |
| Rated Current: | 1.45 A           |

| No-Load Speed:     | 3,650 rpm (+/- 10%) |
|--------------------|---------------------|
| No-Load Current:   | < 300 mA            |
| Stall Torque:      | 1,200 g.cm          |
| Max. Power:        | 11.25 W             |
| Termination Style: | Terminals           |

## **Dimensions**





51

© 2023 ISL Products International Ltd. Specifications subject to change without notice.