



带凸  
D2075WVB1  
-2NP-P0BK G



无凸  
D2075WVB1-2NP-P0BK G

Material:  
Insulator: PBT+30% Glass Fiber (UL94V-0).  
Contact: Copper Alloy with Gold or Tin over Nickel Plated.  
Specification:  
Current Rating: 1 Amp.  
Withstanding Voltage: AC 500V for 1 Minute.  
Insulation Resistance: 1000M Min. W DC 500V.  
Contact Resistance : 15m Max.. W  
Operating Temperature: -40° C ~ +105° C.

**D2075 W V X - 2NP-P0 BK X**

- ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No.
- ② Category: W-wafer
- ③ Welding Board Angle: V- Straight 180°
- ④ Colloid Feature: B-B TYPE(塑宽4.2, 塑高5.4, 带凸)  
B1-B1 TYPE(塑宽4.2, 塑高5.4, 无凸)
- ⑤ Circuit No.: 212-2\*06PIN
- ⑥ Material: P0-PBT,UL94V-0
- ⑦ Color: BK-Black
- ⑧ Plating Method: G-Gold-Plated T-Tin Plated

CKT. SIZE	A	B	C
10	16.65	8.00	11.65
12	18.65	10.00	13.65
14	20.65	12.00	15.65
16	22.65	14.00	17.65
20	26.65	18.00	21.65
22	28.65	20.00	23.65
26	32.65	24.00	27.65
34	40.65	32.00	35.65
40	46.65	38.00	41.65
44	50.65	42.00	45.65
50	56.65	48.00	51.65

					<p>一般公差 GENERAL TOLERANCE</p> <p>.X ±0.3</p> <p>.XX ±0.2</p> <p>.XXX ±0.1</p>				<p><b>EASE</b> EASE ELECTRONICS CO., LIMITED electronics</p>				<p>料号 PART NO D2075WVX-2NP-P0BK G</p>			
					<p>核准 APPD</p>				<p>品名 TITLE 2.0mm Crimp Style connectors</p>							
					<p>审核 CHK</p>				<p>单位 UNIT MM</p>							
					<p>绘图 DR</p>				<p>日期 DATA</p>							
					<p>角法 PROJECT</p>				<p>图号 NUMBER</p>							
					<p>日期 DATE</p>				<p>版次 REV A</p>							
					<p>旧版次 OLD REV</p>				<p>变更内容 DESCRIPTION</p>							
					<p>新版次 NEW REV</p>				<p>审核 CHK</p>							
					<p>核准 APPD</p>				<p>比例 SCALE 1/1</p>							