







环保物料



SPECIFICATION:

Current Rating: 3 A.
 Withstanding Voltage: AC 1000V.
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max..
 Operating Temperature: -40°C ~ +105°C.

Material:

Insulator: PBT+30% Glass Fiber (UL94V-0).
 Contact: Phosphor Bronz
 Contact Plated: Gold over Nickel Plated.

D2553 W V C- 2NP - P0 BK X 1
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
- ② Category: W-Wafer
- ③ Welding Board Angle: V- Straight 180°
- ④ Feature Type: Blank-Normal type,A-A type,B type,C-C type
- ⑤ Circuit No.: 210-2x5PIN~264-2x32PIN,
- ⑥ Material: P0-PBT,UL94V-0
- ⑦ Color: BK-Black
- ⑧ Plating Method: T-Tin-plated, G-Gold-plated,
- ⑨ Options: 1- 3 pieces

						一般公差 GENERAL TOLERANCE .X ±0.3 .XX ±0.2 .XXX ±0.1		EASE EASE ELECTRONICS CO., LIMITED electronics		料号 PART NO D2553WVC-2NP-P0BKX1				
										品名 TITLE 2.54mm IDC Series (C Type) 三件式 (2540HI-2*XPFO3G-PTLG)				
日期 DATE	旧版次 OLD REV	新版次 NEW REV	变更内容 DESCRIPTION	审核 CHK	核准 APPD	角法 PROJECT	核准 APPD	审核 CHK	绘图 DR	日期 DATA	单位 UNIT mm	比例 SCALE 1/1	图号 NUMBER	版次 REV A