



HELUTOP® HT

The plastic cable gland with vibration protection

Properties

- Optimum strain relief through clamping plates
- Easy to assemble
- Large clamping areas

Material

- halogen-free
- phosphor-free
- silicone-free
- cadmium-free

Polyamide PA 6
UV-resistant (RAL 9005)
Seal: Neoprene

Technical data

Protection classification : IP 68 - 5 bar

Temperature range: -30°C up to +80°C

Test standard: EN50262

Note

Details on the international standards see page 34.

metric thread

Part no. light grey RAL 7035	Part no. dark grey RAL 7001	Part no. black RAL 9005	Size Metr.	Cable-Ø from / to mm	Thread mm	length mm	Spanner size mm	Unit	net EUR/100 items at acceptance of		
									up to 100	101 - 500	501 - 1000
93908	93923	93937	M 12 x 1,5	3,0 - 6,5	8,0		15	100	o. r.	o. r.	o. r.
93909	93924	93938	M 16 x 1,5	4,0 - 8,0	8,0		19	50	o. r.	o. r.	o. r.
92667	92668	92669	M 16 x 1,5	5,0 - 10,0	10,0		22	50	o. r.	o. r.	o. r.
93910	93925	93939	M 20 x 1,5	6,0 - 12,0	10,0		24	50	o. r.	o. r.	o. r.
93911	93926	93940	M 25 x 1,5	11,0 - 17,0	8,0		29	50	o. r.	o. r.	o. r.
93912	93927	93941	M 32 x 1,5	15,0 - 21,0	10,0		36	25	o. r.	o. r.	o. r.
93913	93928	93942	M 40 x 1,5	19,0 - 28,0	10,0		46	20	o. r.	o. r.	o. r.
93914	93929	93943	M 50 x 1,5	28,0 - 38,0	18,0		60	10	o. r.	o. r.	o. r.
93915	93930	93944	M 63 x 1,5	34,0 - 44,0	18,0		65	10	o. r.	o. r.	o. r.

metric thread – with reducing seal

Part no. light grey RAL 7035	Part no. dark grey RAL 7001	Part no. black RAL 9005	Size Metr.	Cable-Ø from / to mm	Thread mm	length mm	Spanner size mm	Unit	net EUR/100 items at acceptance of		
									up to 100	101 - 500	501 - 1000
903532	903542	903552	M 12 x 1,5	2,0 - 5,0	8,0		15	100	o. r.	o. r.	o. r.
903533	903543	903553	M 16 x 1,5	3,0 - 7,0	10,0		22	50	o. r.	o. r.	o. r.
903534	903544	903554	M 20 x 1,5	5,0 - 9,0	10,0		24	50	o. r.	o. r.	o. r.
903535	903545	903555	M 25 x 1,5	9,0 - 13,0	8,0		29	50	o. r.	o. r.	o. r.
903536	903546	903556	M 32 x 1,5	11,0 - 15,0	10,0		36	25	o. r.	o. r.	o. r.
903537	903547	903557	M 40 x 1,5	14,5 - 23,0	10,0		46	20	o. r.	o. r.	o. r.
903538	903548	903558	M 50 x 1,5	24,0 - 31,0	18,0		60	10	o. r.	o. r.	o. r.
903539	903549	903559	M 63 x 1,5	29,0 - 35,0	18,0		65	10	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice

o. r. = on request