



## **TECHNICAL BULLETIN: STANDARD-FLEX (HY-TREX®) POWER CABLES Special color-codes**

### **DESIGN RATINGS:**

Voltage	600 (UL) TC-ER 1000 Volt rating WTTC
Temperature	90° C Dry/75° C Wet Max Conductor Temperature
Regulatory	UL: TC-ER, 600 Volt UL: WTTC, 1000 Volt cUL: CIC-TC
Flame Rating	FT4
Cold Bend	-25° C
Conductors	Soft drawn bare copper, finely stranded conductors
Insulation	TPE Compound Color-code: See ordering information
Separator	Non-woven tape separator
Jacket	TPE Compound Color: Black



## ORDERING INFORMATION

PART NUMBER	COND SIZE AWG/# COND	AMPACITY (1)	NOMINAL O.D. (In.)	CABLE WT. (LBS.)/1000 FEET	JACKET COLOR	CONDUCTOR COLOR-CODE
76202Y	16/5	14.4	0.386	102	Yellow	Red, White, Yellow, White/Yellow, Green
76202-ORG	16/5	14.4	0.386	102	Orange	Black, White, Red, Green, Orange
76195GC	14/5	20	0.430	132	Grey	Green/Yellow, Brown, Orange, Yellow, Grey
76200GC	12/4	30	0.452	149	Grey	Green/Yellow, Brown, Orange, Yellow
61804YSP	8/4	55	0.756	433	Yellow	Blue/Yellow-1, Blue/Yellow-2, White/Blue-3, White/Blue-4

(1) – Based on an ambient temperature of 30°C and conductor temperature of 90°C NEC Tables 310.16 & 310.15(C)(1), assume one conductor as ground

**WARRANTY AND DISCLAIMER:** Seller makes no warranties, express or implied, with respect to this product, and seller disclaims any implied warranties of merchantability or fitness for any particular purpose. Further, seller will not be responsible for any consequential, incidental or indirect damages (including, but not limited to, any loss of profit) from any cause whatsoever.

TPC Wire & Cable. All rights reserved. No portion of this publication, whether in whole or in part, can be reproduced without the express written consent of TPC Wire & Cable.