

## TECHNICAL BULLETIN: STANDARD-FLEX (HY-TREX®) POWER CABLES Power Cables with Dedicated Ground Wire

**Design Ratings:** 

Voltage 600 (UL) TC-ER

1000 Volt rating WTTC

Temperature 90° C Dry/75° C Wet Max Conductor Temperature

Regulatory UL: TC-ER, 600 Volt

UL: WTTC, 1000 Volt

cUL: CIC-TC

Flame Rating FT4

Cold Bend -25° C

Conductors Soft drawn bare copper, finely stranded conductors

Insulation TPE Compound

Color-code: Black with White identification

One (1) Green/Yellow Gnd wire

Separator Non-woven tape separator

Jacket TPE Compound

Color: Black



## **ORDERING INFORMATION**

PART NUMBER	POWER COND SIZE	NUMBER OF POWER CONDUCTORS	GROUND CONDUCTOR SIZE (AWG)	AMPACITY (1)	NOMINAL O.D. (In.)
61843-8	4 AWG	3	8	95	1.04
85446	2 AWG	3	6	130	1.12
85246	1 AWG	3	6	145	1.30
61373-2	373 kcmil	3	2	363	2.26

(1) – Based on an ambient temperature of 30°C and conductor temperature of 90°C NEC Tables 310.16 & 310.15(C)(1)

**WARRANTY AND DISCLAIMER:** Seller makes no warranties, express or implied, with respect to this product, and seller disclaims any implied warranties of merchantability or fitness for any particular purpose. Further, seller will not be responsible for any consequential, incidental or indirect damages (including, but not limited to, any loss of profit) from any cause whatsoever.

TPC Wire & Cable. All rights reserved. No portion of this publication, whether in whole or in part, can be reproduced without the express written consent of TPC Wire & Cable.