K-3128BK Automotive Diagnostics Kit



K-3128B

New Automotive Multimeter

3 3/4 Digit 3200 Count Bar Graph Display .25% DCV Accuracy

- 3200 Count, Bar Graph Display
- Dwell Angle: 4, 6. 8 Cylinders ±2%
- Duty Cycle: 0-90%>100µs,<100ms ±2%
- DC Volts to 600 ±0.25%
- AC Volts to 600 ±2%
- AC/DC Current to 10 Amps
- Resistance to 32MOhm
- Frequency 32 kHz
- Temperature -22° to 1400°F
- Diode Test
- Continuity Test
- Data Hold
- Auto Off
- 10 A Fused
- Safety Test Leads
- Safety Input Jacks
- Overload protection on All Ranges

This Automotive Multimeter has all the features necessary to troubleshoot an entire automotive electrical system. It has 0.25% DC voltage accuracy unmatched by any comparably priced instrument. Comes with an operators manual, test leads with test and alligator clips, holster style case and temperature probe.

