



3-150.02 Swinghandle FS PrC with Combination Lock



Avantages

- Resetting the combination is only possible in open position.
- Version c) is supplied with 2 keys.
- IP65 according to DIN EN 60529 - version dish with cap.
- Dish with hook version is secured outside the sealed area.
- RH / LH application.
- Grounding by grounding clip (optional).

Materials

- **Swinghandle:** zinc die, chrome plated or black or PA, black
- **Dish:** PA, black

Notes

(S) Door-thickness 1.5 - 2.5mm
Version c) two opening options:
1. with fixed number code for the combination lock
2. by turning the key in the cylinder. The combination lock is and remains in locked position. The cylinder has the "override" function.



Swinghandle

	Part Number	Latching type	Handle material	Surface handle	Dish	IP protection	Installation type
a)	107-9266.00-00000	combination lock	zinc die	black	with cap	IP65	screw-on

Function

+ extension

d) 3-011 **Grounding Clip Stainless Steel**

* Accessories

3-130 **Rod Latch FS PrC**

3-132.02 **Rod Latch RS PrC**

3-165 **Rod Latch FS PrC and Angle Pieces with Rollers**

3-170 **Rod Latch for Multi-Point Locking FS PrC**

