

3-150.02 Swinghandle FS PrC with Combination Lock



Avantages

Materials

- Resetting the combination is only possible in open position.
- Version c) is supplied with 2 keys.
- IP65 according to DIN EN 60529 version dish with cap.
- Dish with hook version is secured outside the sealed area.
- RH / LH application.
- Grounding by grounding clip (optional).
- Swinghandle: zinc die, chrome plated or black or PA, black
- Dish: PA, black

Notes

(S) Door-thickness 1.5 - 2.5mm
Version c) two opening options:
1. with fixed number code for the combination lock
2. by turning the key in the cylinder. The combination lock is and remains in locked position. The cylinder has the "override" function.



Swinghandle

| | Part Number | Latching type | Handle material | Surface handle | Dish | IP protection | Installation type |
|----|-------------------|--|--------------------|----------------|----------|---------------|----------------------|
| c) | 107-9274.00-00000 | combination lock and keyed alike DIRAK 1333 | PA | black | with cap | IP65 | screw-on |

Function

extension

3-011 Grounding Clip Stainless Steel

* Accessories

+ d)

3-130 Rod Latch FS PrC

- 3-132.02 Rod Latch RS PrC
- 3-165 Rod Latch FS PrC and Angle Pieces with Rollers
- 3-170 Rod Latch for Multi-Point Locking FS PrC

