




75Ω Straight Cable Mount, BNC Connector, Plug, RG6

RoHS Compliant



Stock No.: 0468516C001



Product Description

The High-Definition Television (HDTV) digital technology requires RF connectors with 75Ω impedance showing excellent Return Loss values up to 3GHz. This range of 75Ω connectors which have a broad bandwidth capability are ideally suited for HDTV applications.


General Specifications

Attribute	Value
Coaxial Connector Type	BNC Connector
Gender	Male
Mounting Type	Cable Mount
Impedance	75Ω
Termination Method	Crimp
Body Orientation	Straight
Cable Type	RG6
Bulkhead	No
Operating Frequency	0 to 3GHz
Body Plating	Nickel





Product Drawing



Dimensions: Millimeters (Inches)

Part Number Table

Part Number	Description
0468516C001	75Ω Straight Cable Mount, BNC Connector, Plug, RG6

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.