



50Ω Straight Cable Mount, N Connector, jack RoHS Compliant



- 50Ω Impedance
- N Connector
- Cable Mount



Stock No.: 2956781C024

## Product Description

50 Ohm N series right angle RF coaxial cable plug connectors with screw-on mating and a cable clamp termination.


## **General Specifications**

Attribute	Value
Coaxial Connector Type	N Connector
Gender	Female
Mounting Type	Cable Mount
Impedance	50Ω
Termination Method	Clamp
Body Orientation	Straight
Cable Type	RG11, RG144, RG165, RG213, RG214, RG216, RG393
Operating Frequency	0 to 11GHz
Body Plating	Bronze
Minimum Operating Temperature	-55°C
Maximum Operating Temperature	+155°C
Contact Material	Beryllium Copper
Contact Plating	Gold over Nickel





## **Product Drawing**



Dimensions: Millimeters (Inches)

## **Part Number Table**

Part Number	Description
2956781C024	50Ω Straight Cable Mount, N Connector, jack

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.