




50Ω Straight Cable Mount, SMB Connector, Plug, RG178, RG196 RoHS Compliant



Product Description

50-ohm SMB RF coaxial plug connectors with Snap-On mating and cable clamp connection.


General Specifications


Attribute	Value
Coaxial Connector Type	SMB Connector
Gender	Male
Mounting Type	Cable Mount
Impedance	50Ω
Termination Method	Clamp
Body Orientation	Straight
Cable Type	RG178, RG196
Operating Frequency	0 to 4GHz
Body Plating	Gold
Minimum Operating Temperature	-55°C
Maximum Operating Temperature	+100°C
Contact Material	Beryllium Copper
Contact Plating	Gold over Nickel






Product Drawing







All dimensions are in mm.

Dimensions: Millimeters (Inches)

Part Number Table

Part Number	Description
2955485C035	50Ω Straight Cable Mount, SMB Connector, Plug, RG178, RG196

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.