



50Ω Right Angle Cable Mount, MCX Connector, Plug, RG188, RG316

RoHS Compliant

Stock No.: 2455042C039

FEATURES

- 50Ω Impedance
- MCX Connector
- Cable Mount



Product Description

50 Ohm MCX RF coaxial right angle crimp plug connectors with Snap-On mating and a crimp termination.


General Specifications

Attribute	Value
Gender	Male
Coaxial Connector Type	MCX Connector
Mounting Type	Cable Mount
Impedance	50Ω
Termination Method	Crimp
Body Orientation	Right Angle
Cable Type	RG188, RG316
Operating Frequency	0 to 6GHz
Body Plating	Gold over Nickel
Minimum Operating Temperature	-55°C
Maximum Operating Temperature	+155°C
Contact Material	Brass
Contact Plating	Gold over Nickel





Product Drawing



Dimensions: Millimeters (Inches)

Part Number Table

Part Number	Description
2455042C039	50Ω Right Angle Cable Mount, MCX Connector, Plug, RG188, RG316

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.