

ø 52mm Planetary Gear Motor Carbon - Brushed

MOT-I-80858

Online ID#:

PGM-52-24-676-3-C

Our Planetary Gear Motors are an inline solution providing excellent torque output at various speeds. They are equiped to handle varying loads and are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.



Contact Us for alternative solutions!

Specifications	
Gearhead Type:	Planetary
Motor Type:	Carbon - Brushed
Rated Voltage:	24V DC
Rated Speed:	2.3 rpm
Rated Torque:	168 kg.cm
Rated Current:	2.3 A

No-Load Speed:	3 rpm (+/- 10%)
No-Load Current:	< 0.5 A
Stall Torque:	* 774 kg.cm
Max. Power:	6 W
Reduction Ratio:	676:1
Termination Style:	Terminals

^{*} Gearbox limitations are set at 400 kg.cm, operating past this torque limit may create premature failure.





