



RoHS Compliant

Straight 50Ω RF Adapter BNC Plug to NIM-CAMAC CD/N 549 Plug.

FEATURES

- 50Ω impedance
- BNC Plug to NIM-CAMAC CD/N 549 Plug

Stock No.: 1243438A013



Product Description

Adaptors to facilitate interconnections between common connectors–Straight 50Ω RF Adapter BNC Plug to NIM-CAMAC CD/N 549 Plug


General Specifications

Attribute	Value
Adapter Type A	BNC
Adapter Type B	NIM-CAMAC CD/N 549
Gender A	Male
Gender B	Male
Impedance	50Ω
Body Orientation	Straight
Polarity	Normal
Contact Plating	Gold over Nickel
Length	28.5mm
Body Plating	Nickel
Cable Type	Coaxial
Contact Material	Brass, Bronze





Product Drawing



Dimensions: Millimeters (Inches)

Part Number Table

Part Number	Description
1243438A013	Straight 50Ω RF Adapter BNC Plug to NIM-CAMAC CD/N 549 Plug

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage raising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.