



Customer No:



DST-25MF-CT

\* NTOE: All relevant materials are complied with RoHS directive .



5	RESISTANCE: 1/8W	A7FA01-0161	1	M161	
	LED COLOR RED	A7DA03-0881	9	M881	
	LED COLOR GREEN	A7DA04-0881	9	M881	
	PCB: MSL-3	A7AA03-0730	1	M730	
	DB25 PIN ELECTRO-PLATED HOOD	A4BD03-0016 A4BD06-0016	1set	M16	
4	HEX-NUT 5*6.6mm #4-40	A6BC02-0095	2	M95	
3	SCREW 4*12.5mm, #4-40, ASSEMBLY TYPE	A6AA06-0095	4set	M95	
2	DB25 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	A1AE03-0108	1	M108	
1	DB25 MALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	A1AE14-0108	1	M108	
No.	DESCRIPTION		Q'TY	Supplier	
APPROVED	<b>CompuCableUSA</b> Providing Connectivity Solutions		Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm		
CHECKED					HU
DRAWING					XU
DATE					22/MAY/17
ITEM NO.	DST-25MF-CT & DST-25MF-CT-MF		UNIT:mm		