



⚠ \* NOTE: All relevant materials are complied with RoHS directive .

6	Jumper Wire UL1061/26#/1C x 60mm, OD1.0mm, COLOR WHITE, DRAWING No. EH002601C-013	H5SE06-0304W01	25	M304
5	PCB: MSL-7	A7AA07-0730	1	M730
	ELECTRO-PLATED HOOD	A4BD06-0016	2	M16
4	SCREW 4*12.5mm, #4-40, WITH PAD, ASSEMBLY TYPE	A6AA06-0095	4	M95
3	HEX-NUT 5*6.6mm	A6BC02-0095	2	M95
2	DB25 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	A1AE01-0277U09	1	M277
1	DB25 MALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	A1AE09-0277U09	1	M277

No.	DESCRIPTION		Q'TY	Supplier	
APPROVED	DST-25MF-JP Providing Connectivity Solutions		Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm		
CHECKED					HU
DRAWING					XIAO
DATE	18/MAR/19	ITEM NO.	DST-25MF-JB & DST-25MF-JB-MF	UNIT:mm	