

MIC CROWN

About Item

1. **High-Quality audio:** The contoured frequency response feature ensures that the music produced is **clean and clear**, with great vocal sound quality. It **has a 1/4 (6.35mm) mic in jack**.
2. **Wired & versatile:** The XLR **Neodymium microphone** is ideal for recording **professional-grade music, including drums, percussion, and instrument amplifier**.
3. **Dynamic Karaoke Mic:** The dynamic microphone captures the source sound with its uniform cardioid **pickup pattern while minimizing background noise**.
4. **Sturdy & Build to Last:** 5 Core microphone is incredibly Sturdy & durable and can withstand the rigors of daily use. It has a **frequency response of 50-16000 Hz**.
5. **XLR Cable included:** The dynamic microphone is wired; therefore, it is resistant to jamming and noise free and picks every note from the sound source.

Product Description

Whether performing live or recording in a studio, the music from your instrument can connect with your audience. This includes the **sharp sound of a snare drum**, the melodious notes of an arpeggiated chord, or the **energetic solo of a saxophone**. **These sounds require a microphone that can handle these notes**. The 5 Core dynamic microphone is built to capture your performance's power and deliver it to every listener.

Built with rugged material and a metal mesh **windscreen with an anti-dent ring**, this XLR microphone is designed for maximum reliability, ensuring that it will come through for you time and time again, even after countless gigs and studio applications. Whether you are a seasoned professional or just starting, this versatile, dynamic microphone is a must-have for any performer or recording artist.

At 5 Core, Customer satisfaction is our priority with a proven track record of delivering the highest quality product since 1984.

Features

Compatibility	XLR Cable	Premium Sound	Reliable
The dynamic microphone is compatible with most audio systems, including DVD players, mixers, and home theater.	Fully shielded XLR cable for minimal interference over long distances.	The dynamic microphone provides power and clarity, ideal for studio and stage use.	5 Core microphones are trusted by performers of all levels for their professional utility & high performance.

Technical Specifications

- Type: Dynamic
- Polar Pattern: Cardioid
- Material: Plastic
- Sensitivity: 2 mv/pa
- Frequency response: 50-16000 Hz
- Cable Length: 12 feet

Package Include:

- 1x 12 ft XLR cable
- 1x Dynamic Metal Mic
- 1x Mic Clip

Usages

Wire microphone is ideal for recording instruments.

Use the dynamic microphone for live vocal performance.

A durable microphone is perfect for public events or rallies.

The XLR microphone can be used for podcasts or voice-overs.

The dynamic microphone can be used during a meeting or video conferencing.

Benefits of products

Provides optimal clarity and punch.

Compatible with most PA audio systems.

Minimizes background noise and feedback.

Captures source signal with high accuracy.

Reproduces audio without interference from other instruments or speakers on stage.

Benefits of 5 Core over other products

4.5m coaxial, shielded low noise cable.

Premium-quality ferrite magnet in cartridge.

Universally-matched 3-pin professional XLR connector.

Metal with thick foam for shock/dust proofing cartridge.

5 Core dynamic microphone offers professional-grade sound recording capabilities.

Why 5 Core

5 Core has been known for producing high-quality, premium products since 1984.

We are committed to using only the best materials and components to ensure the longevity of our products.

The best deals compared to other brands in the market without compromising on quality.

The Trustworthy Choice for thousands of customers scattered worldwide in more than 65 countries.

Backed by a proven track record of happy customers and peace of mind.

Comparison

Specification	5 Core Product	Other Product
XLR cable	Yes	No
Durable	Yes	No
Best Deal	Yes	No

About Brand

5 Core, headquartered in California, warehouse in Bellefontaine, OH, USA, has a reputation for being a trusted and reliable brand, offering products designed to meet the highest industry standards. Our products are thoroughly tested and inspected before they are sent to the end user, ensuring that the customers receive products of the highest quality and reliability. With a commitment to quality, affordability, and customer satisfaction, 5 Core is a brand people can trust for all their needs and wants.

Q&A

Question:What is the impedance of the microphone?

Answer:The microphone has a 300 Impedance.

Question:What kind of events is this microphone suitable for?

Answer:This microphone is perfect for all kinds of live events, including presentations, weddings, conferences, singing, and more.

Question:Can I use the XLR microphone for recording in a studio?

Answer:Yes, this XLR microphone is versatile and can be used for stage and recording applications.

Question:What is the frequency response of the dynamic microphone?

Answer:The dynamic microphone has a 50-16000 Hz Frequency response.

Question:What is a cardioid pickup pattern?

Answer:A cardioid pickup pattern is a directional microphone that captures sound mainly from the front of the microphone while minimizing sound from the side and rear. This is ideal for live situations where noise cancellation is needed.