



記號 MARK	ECN NO.	日期 DATE	修改 DRAW	核准 APPROVE

FEATURES:

1 Electrical Test:

- A. Safety Voltage/Current Rating 150V ac, at 1.5A.
- B. Dielectric with standing 1000V/DC/min, <0.5A.
- C. Insulation Resistance: >500M Ω, 1000V./min
- D. Contact Resistance: <20M Ω

2 Mechanical:

- A. Cable-to-Plug tensile strength-20LBs(89N)min.
- B. Durability: 750 mating cycles.
- 3 Operation Temperature: -20°C ~ +80°C.
- 4. Environmental compliance
- A. the products are compliant with the RoHS, and REACH ETC.
- 5. Safety standards: UL E239590

EASE ELECTRONICS CO., LIMITED

品名规格 DESCRIPTION	CONN MOD PLUG 8P8C UNSHIELDED CAT5E			页次 SHEET	1/1
产品编号 PRODUCT NO	RJ45-5U	单位 UNIT	mm	比例 SCALE	1:1
				版本 EDITI	A/0

DIMENSION IN mm(Inch) TOLERANCE UNLESS OTHERWISE SPECIFIED x. x ± 0.2 x. xx ± 0.1 x. xxx ± 0.05	第三视角法 THIRD ANGLE PROJECTION 	制图 DRAWN	王辉	日期 DATE	2023.02.10
	核对 CHECK	李勇波	日期 DATE	2023.02.10	
	批准 APPRO	夏赞华	日期 DATE	2023.02.10	

铜片规格 	胶壳 PC(聚碳酸酯) <input type="checkbox"/> 94-V0 <input checked="" type="checkbox"/> 94-V2	1
	金片 (PIN针) <input checked="" type="checkbox"/> 黄铜 <input type="checkbox"/> 磷铜 Contacts Brass Phosphor copper	8
	<input type="checkbox"/> G/F" <input type="checkbox"/> 1u" <input type="checkbox"/> 3u" <input type="checkbox"/> 6u" <input type="checkbox"/> 15u" <input type="checkbox"/> 30u" <input type="checkbox"/> 50u" <input type="checkbox"/> S"	