



記號 MARK	ECN NO.	日期 DATE	修改 DRAW	核准 APPROVE

FEATURES:

1 Electrical Test:

- A. Safety Voltage/Current Rating 150V ac, at 1.5A.
- B. Dielectric with standing 1000V/DC/min, <0.5A.
- C. Insulation Resistance: >500M Ω, 1000V./min
- D. Contact Resistance: <20M Ω

2 Mechanical:

- A. Cable-to-Plug tensile strength-20LBs(89N)min.
- B. Durability: 750 mating cycles.
- 3 Operation Temperature: -20°C ~ +80°C.
- 4. Environmental compliance
- A. the products are compliant with the RoHS, and REACH ETC.
- 5. Safety standards: UL E239590

**EASE** electronics **EASE ELECTRONICS CO., LIMITED**

品名规格 DESCRIPTION	CONN MOD PLUG 8P8C UNSHIELDED CAT6			页次 SHEET	1/1
产品编号 PRODUCT NO	RJ45-6U	单位 UNIT	mm	比例 SCALE	1:1
				版本 EDITI	A/0

DIMENSION IN mm(Inch)	
TOLERANCE UNLESS OTHERWISE SPECIFIED	
x. x	± 0.2
x. xx	± 0.1
x. xxx	± 0.05

第三视角法  
THIRD ANGLE PROJECTION

制图 DRAWN	王辉	日期 DATE	2023.02.10
核对 CHECK	李勇波	日期 DATE	2023.02.10
批准 APPRO	夏赞华	日期 DATE	2023.02.10

铜片规格

胶壳 PA66(尼龙料)	<input type="checkbox"/> 94-V0	<input checked="" type="checkbox"/> 94-V2	1
金片 (PIN针) Contacts	<input checked="" type="checkbox"/> 黄铜 Brass	<input type="checkbox"/> 磷铜 Phosphor copper	8
<input type="checkbox"/> G/F" <input type="checkbox"/> 1u" <input type="checkbox"/> 3u" <input type="checkbox"/> 6u" <input type="checkbox"/> 15u" <input type="checkbox"/> 30u" <input type="checkbox"/> 50u" <input type="checkbox"/> S"			