


記號 MARK	ECN NO.	日期 DATE	修改 DRAW	核准 APPROVE

**FEATURES:**


- 1 Electrical Test:
  - A. Safety Voltage/Current Rating 150V ac, at 1.5A.
  - B. Dielectric with standing 1000V/DC/min, <0.5A.
  - C. Insulation Resistance: >500M Ω, 1000V./min
  - D. Contact Resistance: <20M Ω
- 2 Mechanical:
  - A. Cable-to-Plug tensile strength-20LBs (89N) min.
  - B. Durability: 750 mating cycles.
- 3 Operation Temperature: -40℃ ~ +85℃.
- 4. Environmental compliance
  - A. the products are compliant with the RoHS, and REACH ETC.
- 5. Safety standards: UL E239590



**EASE ELECTRONICS CO., LIMITED**

排线支架

铜片规格



<input type="checkbox"/> 屏蔽壳 Shell <input type="checkbox"/> 黄铜 Brass <input type="checkbox"/> 铁 Spcc		品名规格 DESCRIPTION <b>CONN MOD PLUG 8P8C UNSHIELDED CAT7</b>		页次 SHEET <b>1/1</b>	
Au: <input type="checkbox"/> G/F" <input type="checkbox"/> 1u" <input type="checkbox"/> 3u" <input type="checkbox"/> Ni <input type="checkbox"/> 80u"		产品编号 PRODUCT NO <b>RJ45-7C</b>		单位 UNIT <b>mm</b> 比例 SCALE <b>1:1</b> 版本 EDITI <b>A/0</b>	
<input type="checkbox"/> 94-V0 <input checked="" type="checkbox"/> 94-V2		DIMENSION IN mm (Inch) TOLERANCE UNLESS OTHERWISE SPECIFIED x, x ±0.2 x, xx ±0.1 x, xxx ±0.05		制图 DRAWN <b>王辉</b> 日期 DATE <b>2022.07.21</b>	
<input type="checkbox"/> 黄铜 Brass <input type="checkbox"/> 磷铜 Phosphor copper		第三视角法 THIRD ANGLE PROJECTION 		核对该 CHECK 日期 DATE <b>2022.07.21</b>	
<input type="checkbox"/> G/F" <input type="checkbox"/> 1u" <input type="checkbox"/> 3u" <input type="checkbox"/> 6u" <input type="checkbox"/> 15u" <input type="checkbox"/> 30u" <input type="checkbox"/> 50u" <input type="checkbox"/> S"		8		批准 APPRO 夏赞华 日期 DATE <b>2022.07.21</b>	