

HL 1820 S

Technical Specifications

Voltage:	120 VAC / 60Hz
Output:	1400 watts
Amps:	11.7
Temperature:	120 / 750 / 1100 °F (50 / 400 / 600 °C)
Airflow rate:	4 / 7 / 13 cfm.
Stages:	3
Highlights:	Higher durability (+20 %) optimized weight balance
Power cord:	Industrial grade rubber, length: 6ft
Motor:	Brush motor
Heating element:	Ceramic heating element
Motor lifetime:	600h
Accessories:	Use of our standard accessories
Dimensions:	9.96" x 3.33" x 7.87" (l x w x h)
Net Weight:	1.77 lbs (28.36 oz)
Single Sell Pack:	Dimensions: 10.20" x 3.54" x 9.33" Weight: 2.18 lbs (34.92 oz)
Country of origin:	Romania
Warranty:	One year limited



UPC-Code

018139375203

Prod. No.

110025541



RoHS
Compliant



double insulated

ISO
9001:
2015
14001:
2015