

HL 1620 S


Technical Specifications

Voltage: 120 VAC / 60Hz
Output: 1300 watts
Amps: 10.8
Temperature: 575 / 950 °F (300 / 500 °C)
Airflow rate: 8 / 13 cfm.
Stages: 2
Highlights: Higher durability (+20 %),
 optimized weight balance
Power cord: Industrial grade rubber, length: 6ft
Motor: Brush motor
Heating element: Micanite heating element
Motor lifetime: 600h
Accessories: Use of our standard accessories

Dimensions: 9.92" x 3.37" x 7.87" (l x w x h)
Net Weight: 1.65 lbs (26.4 oz)
Single Sell Pack: Dimensions: 10.20" x 3.54" x 9.3"
 Weight: 2.06 lbs (32.98 oz)
Country of origin: Romania
Warranty: One year limited



UPC-Code	Prod. No.
018139375104	110023455



RoHS
Compliant



double insulated

ISO
9001:
2015
14001:
2015