

Mobile Heat 3

Cordless Heat Gun

Technical Specifications

Voltage:	18 VAC
Output:	600 watts
Airflow Rate:	7 cfm
Stages:	2
Temperature:	570 or 930 ° F
Motor:	Brush motor
Heating Element:	Ceramic heating element
Display:	Backlight LED
Power Supply:	Rechargeable lithium-ion battery
Thermal Cut-out:	Yes
Accessories:	Case, 5.5 Ah battery & charger, 8 Ah battery & charger
Net Weight:	1.5 lbs, bare tool
Dimensions: (L x W x D)	8.86 x 2.83 x 8.03 inches
Features:	Trigger lock, LED illumination on base of tool, compatible with all standard push-on nozzles and heat guard, rechargeable.
Warranty:	1 year limited



Product No.

Tool w/ Case:	110080696
Tool w/ Case & 8 Ah Battery & Charger:	110084904
8 Ah Battery:	110077820
Charger:	110081184
Mobile Heat Shrink Kit	110093899

Mobile Heat 5

Cordless Heat Gun

Technical Specifications

Voltage: 18 VAC
Output: 900 - 1000 watts

Airflow Rate: 10.5 cfm
Temperature: 120 - 930 ° F

Motor: Brush motor
Heating Element: Ceramic heating element
Display: Digital LCD
Power Supply: Rechargeable lithium-ion battery
Thermal Cut-out: Yes

Accessories: Case, 5.5 Ah battery & charger, 8 Ah battery & charger
Net Weight: 1.5 lbs, bare tool
Dimensions: 8.86 x 2.83 x 8.03 inches
(L x W x D)

Features: Flexible setting options, ready for use within 4 seconds, LCD display for precise settings, 4 preset application specific options, trigger lock, LED illumination on base of tool, compatible with all push-on nozzles and heat guard, rechargeable.

Warranty: 1 year limited



Product No.

Tool w/ Case:	110080698
Tool w/ 8 AH Battery & Charger:	110084905
MH5 Roofing Kit:	110095209
8 Ah Battery:	110077820
Charger:	110081184