



PINOUT:

CUSTOMER P/N:	COLOR	LENGTH(xx)
DBC-25MW-05	BLACK	1525+30/-10mm
DBC-25MW-10	BLACK	3050+30/-10mm
DBC-25MW-15	BLACK	4575+40/-10mm
DBC-25MW-25	BLACK	7625+80/-10mm
DBC-25MW-35	BLACK	10675+80/-10mm

P1 COLOR LABEL		P1 COLOR LABEL	
1	BLACK P1	14	BROWN/BLACK P14
2	BROWN P2	15	RED/BLACK P15
3	RED P3	16	ORANGE/BLACK P16
4	ORANGE P4	17	YELLOW/BLACK P17
5	YELLOW P5	18	GREEN/BLACK P18
6	GREEN P6	19	BLUE/BLACK P19
7	BLUE P7	20	PURPLE/BLACK P20
8	PURPLE P8	21	GRAY/BLACK P21
9	GRAY P9	22	WHITE/BLACK P22
10	WHITE P10	23	PINK/BLACK P23
11	PINK P11	24	BLACK LIGHT GREEN/ P24
12	LIGHT GREEN P12	25	BLACK LIGHT BLUE/ P25
13	LIGHT BLUE P13	Shell	DRAIN

SPEC:

- UL 2464 28AWG*25C+DRAIN+AL JACKET BLACK IN COLOR OD:6.5mm
- DB 25P MALE TYPE BLACK COLOR SHELL NICKEL PLATED
- HEAT SHRINK TUBE LABEL WHITE IN COLOR L=15MM
- MOLDING SCREW 4-40UNC 4*38.5mm
- MOLDING PVC(UL94-V0) BLACK IN COLOR
- DUST CAP

REV	DATE	DESCRIPTION	DRAWN BY	CHECKED BY	SALES	APPROVAL BY			SHEET NO.
A/2	2023.03.13		<i>[Signature]</i>	<i>[Signature]</i>	<i>[Signature]</i>	<i>[Signature]</i>	CompuCableUSA		1/1
			SCALE:	UNIT:MM	DATE: 2023.03.29		P/N: DBC-25MW**		