

1U HIGH DENSITY MPO

1U 128-Core MPO Distribution Cabinet

Features:

- High connectivity density (33% increase over 96-core)
- High deployment efficiency
- Easy operation
- Single panel installation

Applications:

- Data center
- LAN
- Cloud computing
- 19 inch rack



Specifications:

Type	MTP/MPO			
Mode	SM (1310nm/1550nm)		MM (850nm/1300nm)	
	Typical	Low IL	Typical	Low IL
End face	APC	APC	PC	PC
IL (dB)	≤0.6dB	≤0.35dB	≤0.6dB	≤0.35dB
RL (dB)	≥60dB	≥60dB	≥20dB	≥25dB

Type	LC	
Mode	SM (1310nm/1550nm)	MM (850nm/1300nm)
	IL (dB)	≤0.35dB
IL (dB)	≥50dB	≥25dB

1U 256-Core MPO Distribution Cabinet

Features:

- Ultra high connectivity density (167% increase over 96-core)
- High deployment efficiency
- Easy operation
- Single panel installation

Applications:

- Data center
- LAN
- Cloud computing
- 19 inch rack



Specifications:

Type	MTP/MPO			
Mode	SM (1310nm/1550nm)		MM (850nm/1300nm)	
	Typical	Low IL	Typical	Low IL
End face	APC	APC	PC	PC
IL (dB)	≤0.6dB	≤0.35dB	≤0.6dB	≤0.35dB
RL (dB)	≥60dB	≥60dB	≥20dB	≥25dB

Type	LC	
Mode	SM (1310nm/1550nm)	MM (850nm/1300nm)
	IL (dB)	≤0.35dB
IL (dB)	≥50dB	≥25dB



Crowntech
P H O T O N I C S

**LET US SOLVE YOUR
COMPONENTS AND
SOLUTIONS LEAD TIMES**

CONTACT US TODAY!

sales@crowntechphotonics.com

www.crowntechphotonics.com

