Identification tags for cable bundle, thermal transfer

TIPTAG HF- Rail Limited Fire Hazard, Halogen free

The Tiptag HF cable markers have designed to identify larger wires and cable bundles not only in the electronics and general cabling environments but also in the railway industry. Tiptag HF is halogen free and its material properties show low smoke propagation, density and toxicity. Tiptags are presented in a special perforated format which include fastening slots for easy fitting with cable ties. They are also suitable for retrofit purposes.

Print from the reel with HellermannTyton's premium range of thermal transfer printers and ribbons for optimum print quality and longevity.

Features and benefits

- Ideal for marking larger wire and cable bundles
- · Halogen free
- Low smoke propagation and toxicity
- Perforated format that includes fastening slots for cable ties
- Available in white, yellow, blue and red




TIPTAG - High performance cable bundle marking.

| MATERIAL | Polyolefin (PO) | | |
|----------------------------|---|--|--|
| Operating Temperature | -40 °C to +90 °C | | |
| Flammability | Limited Fire Hazard, low generation of toxic gases and corrosive acid, low smoke generation, halogen free | | |
| Recommended Ribbon Type | TTDTHOUT | | |
| Thermal Transfer Printer | TT430, TT4030 | | |










| ТУРЕ | Length | Width | Pack | C-1 | 0.4:-1- 0 |
|----------------|--------|-------|----------|-------------|-------------|
| ITPE | (L) | (W) | Cont. | Colour | Article-No. |
| TIPTAG11X65BU | 65.0 | 11.0 | 190 pcs. | Blue (BU) | 556-20066 |
| TIPTAG11X65RD | 65.0 | 11.0 | 190 pcs. | Red (RD) | 556-20062 |
| TIPTAG11X65WH | 65.0 | 11.0 | 190 pcs. | White (WH) | 556-20069 |
| TIPTAG11X65YE | 65.0 | 11.0 | 190 pcs. | Yellow (YE) | 556-20064 |
| TIPTAG15X65WH | 65.0 | 15.0 | 190 pcs. | White (WH) | 556-21069 |
| TIPTAG15X65YE | 65.0 | 15.0 | 190 pcs. | Yellow (YE) | 556-21064 |
| TIPTAG11X100BU | 100.0 | 11.0 | 120 pcs. | Blue (BU) | 556-20080 |
| TIPTAG11X100RD | 100.0 | 11.0 | 120 pcs. | Red (RD) | 556-20091 |
| TIPTAG11X100WH | 100.0 | 11.0 | 120 pcs. | White (WH) | 556-20079 |
| TIPTAG11X100YE | 100.0 | 11.0 | 120 pcs. | Yellow (YE) | 556-20074 |
| TIPTAG15X100RD | 100.0 | 15.0 | 120 pcs. | Red (RD) | 556-21096 |
| TIPTAG15X100WH | 100.0 | 15.0 | 120 pcs. | White (WH) | 556-21079 |
| TIPTAG15X100YE | 100.0 | 15.0 | 120 pcs. | Yellow (YE) | 556-21074 |

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available. More colours on request.



For product specific approvals and specifications please refer to the Appendix.

