

## mp-IM1



Inkjet systems

### PRODUCT INFORMATION

The lightweight and compact mp-IM1 inkjet printer from Murrplastik is quick and flexible to use and especially suitable for small print jobs.

It convinces particularly by its fast printing speed and its extremely fast drying ink, which allows the inscribed sign to be inserted immediately after printing. The mp-IM1 can be used to mark all Murrplastik baseplate bound polycarbonate signs with the specially developed black ink. The modular design of the device and the unit of print head and cartridge also make for a stable and easy-to-maintain system.

#### Specification

- Print area: 120 x 120 mm
- Print speed: approx. 8 seconds / frame
- Print resolution: 300 x 300 dpi
- Ink: special surface-dissolving black ink
- Print quantity: approx. 1,000,000 characters, Arial font, font size 9, PDF Creator

- Ink cartridges: 1
- Input voltage: 110 – 240 V AC
- Frequency: 50 – 60 Hz
- Power consumption: 20 W at pressure / 0.3 W switched off
- Ports: USB 2.0 / Ethernet
- Unit dimensions B x H x T (31 x 18 x 38) cm
- Weight: approx. 6 kg

#### Scope of delivery

- mp-IM1 printer
- Ink cartridge
- mp-IM1 Carrier plate
- Power cable with power supply unit
- USB data cable
- Service station (built-in)
- Absorbent fleece (built-in)
- Driver CD
- Operating instructions
- Shipping box

### SPECIFICATIONS



Type	Order No.	MOQ qty.
<b>Printer system</b>		
mp-IM1 Inkjet marking system	86625200	1
	86625211	1
	86625212	1
<b>Consumables</b>		
mp-IM1 Tintenpatrone EK-PC 3.1	86625205	1
<b>Spare parts</b>		
mp-IM1 Vlies-Box	86625215	1
mp-IM1 Service-Station	86625210	1
mp-IM1 Ersatzverpackung komplett	86625220	1
<b>Accessories</b>		
mp-IM 1 Reinigungs-Set	86625206	1

## mp-IM1

### LABELLING TECHNOLOGY



All details given in our sales brochures and catalogues, as well as the information available online, are based on our current knowledge of the products described.

The electronic data and files made available by Murrplastik, particularly CAD files are based on our current knowledge of the product described.

A legally binding assurance of certain properties or the suitability for a certain purpose can not be determined from this information.

All information with respect to the chemical and physical properties of Murrplastik products, as well as application advice given verbally, in writing or by tests, is given to the best of our knowledge.

They do not release the buyer from the obligation to carry out his own tests and trials in order to determine the concrete suitability of the products for the intended purpose.

Murrplastik accepts no responsibility for the available information being up-to-date, correct or complete. Neither do we accept responsibility for the quality of this information.

Murrplastik accepts no liability for damage caused as a result of using our products.

Murrplastik reserves the right to make technical changes and improvements through constant further development of products and services.

Our General Terms and Conditions apply.

© Murrplastik Systemtechnik GmbH • proID\_132127~20210526~890286~ACS\_MPIM1\_DRUCKER